

# Clean air. From a little yellow box.



## Clean Air Box Series (CAB) Breathing Air Filtration Systems

### COMPLIANCE

OSHA requires that employers provide their workers with Grade D breathing air. Bullard Clean Air Boxes provide 3-stage filtration and carbon monoxide (CO) monitoring to help meet this requirement.

### DESIGN

#### Rugged construction for harsh work environments

- Polycarbonate Pelican® Cases (Portable Units)
- Powder Coated Steel (Wall Mount Units)

#### Automatic condensate drains extend filter element life

Independent regulators (optional) ensure each worker has the proper air flow

### 3-STAGE FILTRATION

Three stages of filtration remove oil, water, particulate, oil vapor and odors.

- First Stage - Removes 95% of solid contaminants and bulk liquids from the breathing air, down to five microns, prolonging the life of the second and third stage elements.
- Second Stage - Removes extremely fine oil mists down to .01 microns. Maximum remaining filter efficiency is 99.9998%.
- Third Stage - Removes unpleasant oil and hydrocarbon vapors and odors from the air. Maximum remaining oil content is .003 ppm by weight. Filter efficiency is 99.9998%.

Filter change indicators visually alerts the operator to replace element

Replacement filters compatible with other brands of filtration panels

### CO MONITORING

Auto calibration takes approximately 90 seconds and requires no tools

High intensity 90 dB alarm remote capable with strobe

#### Self-contained

- 70+ hours of operation on 8-AA batteries
- 110VAC power cord included

Visual display with internal LCD and External LEDs



# Clean Air Box Series (CAB)

## Technical Specifications and Ordering Information



### Technical Specifications

#### Filtration Capacity

15 cfm	(425 lpm) at 110 psi (7.5 bar)
50 cfm	(1415 lpm) at 110 psi (7.5 bar)
30 cfm	(850 lpm) at 110 psi (7.5 bar)
100 cfm	(4248 lpm) at 110 psi (7.5 bar)

#### Filter Efficiency

First Stage:	Filters down to 5 microns. 95% of bulk liquids. Automatic drain. Filter Change Indicator.
Second Stage:	Filters down to .01 microns. 99.9998% efficient. Automatic drain. Filter Change Indicator.
Third Stage:	Removes oil vapors, odors and tastes. Maximum remaining oil content .003 ppm/wt. 99.9998% efficient. Filter Change Indicator.

#### Filter Housing

Inlet	Polycarbonate bowls.
Outlets	1/2" (13mm) Industrial Interchange (Hansen Compatible) male plug
Max Inlet Pressure	1,2,4, or 8 as specified. 1/4" Hansen quick disconnect standard. Schrader, Snap Tite, CEJN also available Aluminum block manifold
Max Outlet Pressure	150psi (10.3 bar)
Relief Valve	125psi (8.6 bar) ASME preset

Pressure Regulator Construction	Adjustable locking regulator with 0-160 psi outlet gauge. Wall Panel Units - steel with powder coating
---------------------------------	--

#### Portable Units

Polycarbonate Pelican case

#### Monitor

Flow-thru In-line continuous operation

#### Voltage

Portable Units: 115-volt AC (10' cord included) or 8-AA batteries. Monitor switches automatically to DC with AC power failure

#### Display

Wall Units: 110/220 VAC, wiring required. Internal digital LCD display

#### Operation Lights

Accurate +/- 1% of full scale  
External green light - normal AC operation  
External red light - high CO  
External amber light (steady) - battery power in use  
External amber light flashing - low battery with flashing chirp  
High intensity 90 dB

#### Audible Alarm

#### Response

90% of full scale in 10 seconds

#### Sensor

Electrochemical (CO specific)

#### Output Signal

Remote alarm jack with DC output and cover cap

#### Calibration

Autocalibration (no tools required). Completes in 90 seconds. Recommended monthly.

#### Warranty

Two years on sensor and monitor

### Ordering Information

#### Portable Units\*

CAB15	15 cfm with one outlet
CAB30	30 cfm with two outlets
CAB30IR	Same as above with Independent Regulators
CAB50	50 cfm with four outlets
CAB50IR	Same as above with Independent Regulators
CAB100	100 cfm with eight outlets
CAB100IR	Same as above with Independent Regulators

#### Wall Units\*

CAB15PM	15 cfm with one outlet
CAB30PM	30 cfm with two outlets
CAB30PMIR	Same as above with Independent Regulators
CAB50PM	50 cfm with four outlets
CAB50PMIR	Same as above with Independent Regulators
CAB100PM	100 cfm with eight outlets
CAB100PMIR	Same as above with Independent Regulators

#### Replacement Parts

CAB30FEA	Stage 1 Element for 15 or 30 cfm
CAB30FEB	Stage 2 Element for 15 or 30 cfm

#### Replacement Parts

CAB30FEC	Stage 3 Element for 15 or 30 cfm
CAB30FK	Element kit, includes Stages 1-3 for 15 or 30 cfm
CAB50FEA	Stage 1 Element
CAB50FEB	Stage 2 Element
CAB50FEC	Stage 3 Element
CAB50FK	Element kit, includes Stages 1-3
CAB100FEA	Stage 1 Element
CAB100FEB	Stage 2 Element
CAB100FEC	Stage 3 Element
CAB100FK	Element kit, includes Stages 1-3
CABRS	CO Monitor Sensor Element

#### Accessories

CABCK	Calibration Kit
RA	Remote Alarm
CABKS1530**	Kickstand FOR CAB15 or CAB30
CABKS50100**	Kickstand FOR CAB50 or CAB100

\*Specify outlet fitting when ordering  
\*\*Must be ordered with Clean Air Box

### ⚠ WARNING

These units will not remove Carbon Monoxide (CO), Carbon Dioxide (CO<sub>2</sub>), Nitrogen, or other toxic gases or fumes. These units will not increase the oxygen content of an air supply and should not be used when air entering the system is oxygen deficient. Air filtration systems must be operated in the upright position to allow the auto drains to properly seat. The standard Clean Air Box (CAB) filtration units are not explosion proof and should be located in a non-explosive environment.

Bullard products are manufactured to exacting specifications. Any alteration or modification of these products by the user may adversely affect product performance. This information is in summary form only for easy reference. Refer to labels, instruction sheets and other literature accompanying the product for more complete details regarding product installation, use, maintenance, warnings, performance capabilities, complete specifications, user instructions and precautions.

#### Americas:

**E.D. Bullard Company**  
1898 Safety Way  
Cynthiana, KY 41031-9303  
Toll free: 877-BULLARD (285-5273)  
Tel: 859-234-6616  
Fax: 859-234-8987  
[www.bullard.com](http://www.bullard.com)

#### Europe:

**Bullard GmbH**  
Lilienthalstrasse 12  
53424 Remagen • Germany  
Tel: +49-2642 999980  
Fax: +49-2642 9999829  
[www.bullardextrem.com](http://www.bullardextrem.com)

#### Asia-Pacific:

**Bullard Asia Pacific Pte. Ltd.**  
LHK Building  
701, Sims Drive, #04-03  
Singapore 387383  
Tel: +65-6745-0556  
Fax: +65-6745-5  
[www.bullard.com](http://www.bullard.com)